

# Professionally approved products. Datasheet

# PUR 25m Long transparent Flexible Tube Reinforced, 82mm Bend Radius, Applications Various

## RS Stock number 339-6297



SIZES:

#### APPLICATION EXAMPLES:

Conveyance of gases, liquid,

dry powders and granules (especially where good abrasion

characteristics are required).

Available in 30m coils

COLOURS:

Clear

### CPR SERIES

A polyurethane hose with outstanding elasticity providing excellent flexibility and kink-resistance, even in extreme cold conditions.

#### KEY FEATURES:

Ultra-flexible in low temperature environments.
Exceptional abrasion resistance.
Resistant to a wide range of chemicals.
Compliant with F&DA regulations.
Excellent clarity for clear visibility.
High levels of kink resistance and good memory.
85 Shore A hardness.
Service Temperature -40°C to + 65°C.

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.