

Professionally approved products.

Datasheet

RS Cable Marker Application Tool for Helagrip Cable Markers Sizes B & C

RS Stock number: 404-409



Material: Cooper / Brass Alloy (Bronze) Cable Marker Application Tool Shaft

Finish: Rough PTFE (Teflon) Coating Finish for Application Tools

Contents:

1 PC – 2.0 MM (ID) Cable Marker Application Tool for “HELAGRIP” Markers A with Teflon Coating (Cable Diameter Range: 0.58 ~ 0.78 MM² / HG 1.0~ 3.0 MM) and Overall Length 66.0 MM, Diameter of Shaft – 2.70 MM, Length of Tip Chamfer – 15.0 MM, Diameter for Wire Application Hole - 2.0MM and Hole Depth - 20.0 MM) (Part No: PD-0541)

RS Item No:	Description	Application Cable Diameter Range
404-405 (PD-0542)	3.3 MM ID	Range: 0.70 ~ 4.00 MM ² (HG: 2.0 ~5.0 MM)
404-409 (PD-0543)	4.6 MM ID	Range: 4.00 ~ 16.00 MM ² (HG: 4.0 ~9.0 MM)

Overall Length	Diameter of Shaft	Length of Chamfer	Diameter of Hole	Depth of Hole
66.0 MM	2.70 MM	15.0 MM	2.00 MM	20.0 MM
81.0 MM	4.30 MM	25.0 MM	3.30 MM	20.0 MM
87.5 MM	5.80 MM	35.0 MM	4.60 MM	20.0 MM