





# 25 Pin D-Hood-2

RS Stock Number 5444398


| NO | DESCRIPTION  | DATE      |
|----|--|-----------|
| △  | ADD MIS PART NO.   | 04.01.04' |
| △  | ADD A-A SECTION<br>φ2.7 → φ2.7 <sup>+0.1</sup> <sub>-0</sub> | 12.02.04' |
| △  | ADD (P/N:544-4398)   | 04.14.10' |
| △  | 3.0 → 2.8  | 06.28.10' |




△ A-A SECTION




⑥



③



④



⑤

△ MIS PART NO: 069-0025H-02 (P/N:544-4398) △

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

| NO | DESCRIPTION | MATERIAL | Q'TY | FINISH |
|----|-------------|----------|------|--------|
| 6  | SPRING      | IRON     | 1    | ZINC   |
| 5  | SCREW       | IRON     | 2    | ZINC   |
| 4  | SCREW       | IRON     | 2    | ZINC   |
| 3  | SCREW       | IRON     | 2    | ZINC   |
| 2  | CAP         | ABS      | 1    | NICKEL |
| 1  | BODY        | ABS      | 1    | NICKEL |

| DESCRIPTION |          | 25PIN D-HOOD-1 |                | DATE            | REV. |
|-------------|----------|----------------|----------------|-----------------|------|
| 製圖          | DRAWN    | TOLERANCE      | 品名             | 日期              | 版次   |
|             | Yoko     | X ±0.2         | 25PIN D-HOOD-1 | 10.30.96'       | A-4  |
| 檢圖          | CHECK    | .XX ±0.1       | TITLE          | ROHS COMPLIANT  |      |
|             | Angela   | .XXX ±0.05     | 單位             | DWG.NO. 55-0082 |      |
| 認定          | APPROVAL | ANGLE ±5°      | 比例             | SCALE           |      |
|             | Angela   |                | 2:1            |                 |      |

