speco technologies

2.4 GHz Intelligent Frequency Wireless Microphone Kits

M24GHK 2.4 GHz wireless microphone receiver with handheld transmitter

M24GLK 2.4 GHz wireless microphone receiver with bodypack transmitter and lapel clip microphone

M24HS

Optional headset microphone for use with bodypack transmitter

Features

- · Each kit includes either a handheld or bodypack transmitter
- Bodypack transmitter comes with a lapel clip microphone
 Headset microphone available for bodypack transmitter
- to allow more active use (order part# M24HS) • Intelligent frequency hopping to help avoid interference
- Easy one-button setup
- · Recommended 50' transmission range



Receiver Specifications:

Modulation	GFSK
Frequency	2404 ~ 2476 MHz
Distortion THD	<0.05%@1kHz
RF Sensitivity	-78dBm
S/N	>85dB
Audio Output Level	0dBu (770mV)
Power Supply	DC12V, 200mA (included)
Channels	16
Frequency Response	20Hz ~ 18kHz, +/- 3dB
System Latency	8ms

Transmitter Specifications:

manormittor opoor	noutiono.
Modulation	GFSK
Frequency	2404 ~ 2476 MHz
Transmit Power	8dBm (typical)
Distortion THD	<0.05%@1kHz
S/N	>85dB
Consumption Current	<85mA (at 3V)
Power Supply	2 x 1.5V "AA" batteries (not included)
Usage Time	Approximately 20 hours
Channels	16
Frequency Response	20Hz ~ 18kHz, +/- 3dB
Bandwidth	2Mhz

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/22/15