

Digital AM/FM Tuner with 30 presets and 1 Watt Output

PFA

Features

- · 30 station presets
 - 18 FM presets (3 groups of 6)
 - 12 AM presets (2 groups of 6)
- · Scan and seek functions
- Auto-store memory function
- · Preset memory scan function
- Stereo line level out
- Adjustable mono output up to 1W power for a standalone Music-on-hold system
- · Signal strength indicator
- · Rack mount kit included
- AM/FM antenna included
- Connection for 12/24V Battery Backup
- Standard 1 RU rack chassis



rear of unit

Specifications

Tuning Range	. AM: 530kHz ~1620kHz
	FM: 87.5MHz ~ 108.0 MHz
Antenna Input	. AM: Single conductor lead wire
	FM: 300 Ohms twin lead or 75 Ohms coax
Usable Sensitivity	. AM: 4.5uV
	FM: 2uV
Signal to Noise Ratio	. AM: 50dB
	FM: 60dB
Output Levels	. Line: 775mV (0dBm) Unbalanced
	Music-on-hold: 775mV (0dBm) Balanced
Station Memory Backup	. 45 days (after AC power turned off)
Power Source	. 15W
THD	Less than 1% @1KHz
Signal/Noise Ratio	. Microphone: >60dB / TEL: >60dB / Line: >70 dB
Controls	Power, Volume, Tuner (controls and presets)
Telephone	. MoH Out
Indicators	. Power, power level, tuner LCD
Includes	. Rack-mount hardware
Dimensions	. 16.5" (W) x 1.7" (H) x 8.3" (D)
Weight	.7.1 Lbs.

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/30/14