




NO	DESCRIPTION	DATE
△	ADD 5.0 MAX. PANEL	06.11.12'
△	ADD VSWR	07.30.12'
△	DEL. PROOF VOLTAGE WORKING VOLTAGE → VOLTAGE RATING	04.15.13'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-4 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 500 VOLTS MAX. △
- 1.4 VSWR: 1.5 MAX. △

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +80° C

APPROVED by _____ DATE: _____

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
7	WASHER	BRASS	1	NICKEL
6	CENTER CONTACT	BRASS	1	GOLD
5	INSULATION	ABS	1	NONE
4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	INSULATION	TEFLON	2	NONE
2	WASHER	STEEL	1	NICKEL
1	NUT	BRASS	1	NICKEL



DESCRIPTION		STRAIGHT BNC ISOLATED BULKHEAD JACK-JACK ADAPTER	
製圖	DRAWN	TOLERANCE	品名
Kristina	X	±0.2	13-29-7 T.G.N
檢圖	CHECK	單位	日期
Arc	.XX	±0.1	06.17.97'
認定	APPROVAL	比例	版次
Angela	.XXX	±0.05	B-3
	ANGLE	±5°	DWG.NO. 13-0210
			SCALE 4:1
			5463787