



# SPECIFICATION SHEET

## 385-FRRJ



### FR DUAL CERTIFIED STANDARD JEANS

- Arc Rating: ATPV 16.4 cal/cm<sup>2</sup>
- Denim 13oz FR
- Contrast Topstitching with Aramid high tenacity FR thread
- All metal thermally protected from the skin
- Bar-tacked at all stress points
- One-way heavy duty #5 brass zipper on aramid tape
- 2 curved waist pockets, 1 coin pocket at right side, 2 rear hip patch pockets, hammer loop on left leg and tool pocket on right leg
- One set copper jeans button at front waistband

### STANDARDS MET

- NFPA 70E / ASTM F1506
- NFPA 2112-2012
- NFPA 1975-2009
- CAN/CGSB 155.20-2000, CAN/CGSB 155.22-97, et OSHA 29 CFR 1910.269
- EN ISO11611:2008, EN ISO11612:2008, EN ISO14116:2008

### APPLICATIONS

- Electrical & utilities
- Petrochemical, oil & gas
- Mining
- Welding

### CARE INSTRUCTIONS

Machine wash warm, tumble dry low. Wash with synthetic detergents. Wash separate from everyday clothing in small loads FR clothing is dry cleanable. DO NOT use bleach, fabric softener or dryer sheets



### TECHNICAL DATA


MATERIAL	100% Cotton
CONSTRUCTION	<b>Main:</b> Denim FR twill weave <b>Acc:</b> Aramid high tenacity FR thread
COLOR	■ Blue Denim
SIZES	30 x 30 - 50 x 36
PACKAGING	1/Polybag
CASE	20.5" x 15.4" x 9.1" / 52cm x 39cm x 23cm
CASE WEIGHT	22 lbs / 10kg
COO	China

### DIMENSIONS (in)

	30	32	34	36	38	40	42	44	46	48	50	
<b>A</b>	--	31.5	33.5	35.5	37.5	39.5	41.5	43.5	45.5	47.5	49.5	51.5
	30	31.75	31.75	31.75	31.75	31.75	31.75	31.75	31.75	31.75	31.75	31.75
<b>B</b>	32	33.75	33.75	33.75	33.75	33.75	33.75	33.75	33.75	33.75	33.75	33.75
	34	35.75	35.75	35.75	35.75	35.75	35.75	35.75	35.75	35.75	35.75	35.75
	36	37.75	37.75	37.75	37.75	37.75	37.75	37.75	37.75	37.75	37.75	37.75

### BARCODES (Continues on next page)

ITEM	EACH	BOX	CASE
385-FRRJ-3030	616314163425	01616314163424	02616314163423
385-FRRJ-3032	616314163432	01616314163431	02616314163430
385-FRRJ-3034	616314163449	01616314163448	02616314163447
385-FRRJ-3036	616314163456	01616314163455	02616314163454
385-FRRJ-3230	616314163463	01616314163462	02616314163461
385-FRRJ-3232	616314163470	01616314163479	02616314163478
385-FRRJ-3234	616314163487	01616314163486	02616314163485
385-FRRJ-3236	616314163494	01616314163493	02616314163492





# SPECIFICATION SHEET

## 385-FRRJ

### BARCODES (Continued)

385-FRRJ-3430	616314163500	01616314163509	02616314163508
385-FRRJ-3432	616314163517	01616314163516	02616314163515
ITEM	EACH	BOX	CASE
385-FRRJ-3434	616314163524	01616314163523	02616314163522
385-FRRJ-3436	616314163531	01616314163530	02616314163539
385-FRRJ-3630	616314163548	01616314163547	02616314163546
385-FRRJ-3632	616314163555	01616314163554	02616314163553
385-FRRJ-3634	616314163562	01616314163561	02616314163560
385-FRRJ-3636	616314163579	01616314163578	02616314163577
385-FRRJ-3830	616314163586	01616314163585	02616314163584
385-FRRJ-3832	616314163593	01616314163592	02616314163591
385-FRRJ-3834	616314163609	01616314163608	02616314163607
385-FRRJ-3836	616314163616	01616314163615	02616314163614
385-FRRJ-4236	616314165368	01616314165367	02616314165366
385-FRRJ-4430	616314165375	01616314165374	02616314165373
385-FRRJ-4432	616314165382	01616314165381	02616314165380
385-FRRJ-4434	616314165399	01616314165398	02616314165397
385-FRRJ-4436	616314165405	01616314165404	02616314165403
385-FRRJ-4630	616314165412	01616314165411	02616314165410
385-FRRJ-4632	616314165429	01616314165428	02616314165427
385-FRRJ-4634	616314165436	01616314165435	02616314165434
385-FRRJ-4636	616314165443	01616314165442	02616314165441
385-FRRJ-4830	616314165450	01616314165459	02616314165458
385-FRRJ-4832	616314165467	01616314165466	02616314165465
385-FRRJ-4834	616314165474	01616314165473	02616314165472
385-FRRJ-4836	616314165481	01616314165480	02616314165489
385-FRRJ-5030	616314165498	01616314165497	02616314165496
385-FRRJ-5032	616314165504	01616314165503	02616314165502
385-FRRJ-5034	616314165511	01616314165510	02616314165519
385-FRRJ-5036	616314165528	01616314165527	02616314165526