



<b>LED/Multiled</b>	<i>LED</i>	<b>Optimum voltage (V)</b>	<i>24vdc</i>	<b>Intensity</b>	<i>900mcd</i>
<b>Mounting Size</b>		<b>Rectifier</b>			
<b>Mounting Finish</b>		<b>AC current</b>			
<b>Protection</b>		<b>DC current</b>	<i>15mA</i>		
<b>Mount Holder</b>	<i>T5.5 Slide Base</i>	<b>Voltage Tolerance(%)</b>	<i>10%</i>		
<b>Chip Qty</b>	<i>1</i>	<b>Optimum temperature (°C)</b>	<i>-30°C...+60°C</i>		
<b>Indicator colour</b>	<i>Blue</i>	<b>Storage temperature (°C)</b>	<i>-30°C...+60°C</i>		
<b>Wavelength (nm)</b>	<i>470</i>	<b>Contact Tab x 2</b>	<i>T5.5 Slide Base</i>		



*Dimension in mm (typical), not to scale.  
We reserve the right to make changes without further notice to this product to improve reliability, function or design.*