



Note:

- Maximum Insertion loss = 0.3dB
- Attenuation (dB/km): (1310/1550nm), (0.38/0.24)
- Primary Buffer Diameter = 0.25mm
- Components to be ROHS compliant
- Cable material to be LSZH
- Tolerances:
 L -0/+100 (for L<0.5m)
 L -0/+150 (for 0.5m>L<5m)
 L -0/+200 (for L>5m)

ITEM NO.	PART NUMBER	QTY.
1	LC White Boot	2
2	Yellow Heat Shrink	2
3	Serial Number Label	1
4	LC Simplex Single Mode Connector (blue)	2
5	2mm OD Yellow Simplex Single Mode Cable	1

		UNLESS OTHERWISE SPECIFIED:		NAME	DATE	TITLE: LC-LC Single Mode Simplex Patchcord			
		DIMENSIONS ARE IN mm		DRAWN	A Hellyer			27/03/2006	
		TOLERANCES:		CHECKED	S Harvey			27/03/2006	
		FRACTIONAL ±		ENG APPR.	Yes			27/03/2006	
		ANGULAR: MACH ± BEND ±		MFG APPR.					
		TWO PLACE DECIMAL ±		Q.A.			SIZE	DWG. NO.	REV
		THREE PLACE DECIMAL ±		COMMENTS:			A	060327-3	1
		INTERPRET GEOMETRIC TOLERANCING PER:		Standard Configuration			SCALE: NTS	WEIGHT:	SHEET 1 OF 1
		MATERIAL							
NEXT ASSY	USED ON	FINISH							
APPLICATION		DO NOT SCALE DRAWING							

5

4

3

2

1