

Professionally approved products.

## Datasheet

# 20kΩ DO-35 Measurement NTC Thermistor



Stock Number	R (25 °C) Ω	B value K (25-85°C)	B value tolerance ±%	Dissipation constant mW/°C	Time constant s	Min operating temp °C	Max operating temp °C	Availability of resistance tolerance at 25°C			
								±10%	±5%	±4%	±3%
198-927	10000	3960	1	3.0	7	-55	250	*	*	*	*
198-933	20000	3960	1	3.0	7	-55	250	*	*	*	*
198-949	30000	3960	1	3.0	7	-55	250	*	*	*	*
198-955	50000	3960	1	3.0	7	-55	250	*	*	*	*
198-961	100000	3960	1	3.0	7	-55	250	*	*	*	*

### Coding

The above codes refer to bandoliered devices with +10% resistance tolerance at 25°C:

For +5% resistance tolerance replace B10 in code by B5

For +4% resistance tolerance replace B10 in code by B4

For +3% resistance tolerance replace B10 in code by B3

For loose-packing replace B in code by N

### Dimensions: (mm)

