


**RS ITEM NO 207-567**



<b>LED/Multiled</b>	<i>LED</i>	<b>Optimum voltage (V)</b>	<i>6Vac/dc</i>	<b>Intensity</b>	<i>265mcd</i>
<b>Mounting Size</b>	<i>10x25mm</i>	<b>Rectifier</b>	<i>Protection Diode</i>	<b>Reverse Voltage</b>	<i>80V(max)</i>
<b>Mounting Finish</b>	<i>Ba9s</i>	<b>AC current</b>	-		
<b>Protection</b>	-	<b>DC current</b>	<i>13mA (max)</i>		
<b>Mount Holder</b>	<i>Ba9s</i>	<b>Voltage Tolerance(%)</b>	<i>10%</i>		
<b>Chip Qty</b>	<i>1</i>	<b>Optimum temperature (°C)</b>	<i>-25°C...+60°C</i>		
<b>Indicator colour</b>	<i>Blue</i>	<b>Storage temperature (°C)</b>	<i>-25°C...+60°C</i>		
<b>Wavelength (nm)</b>	<i>470</i>	<b>Contact Tab</b>	<i>Ba9s Cap</i>		



*Dimension in mm (typical) not to scale  
We reserve the right to make changes without further notice to his product to improve reliability, function or design*

