



Datasheet

Stock No: 215-855

ENGLISH

RS Pro M3 HSS Teeth; Alloy Steel Body 92mm Bi-Metal Hole Saw



Product Details

RS Bi-metal hole saws

Hardened cutting edge (6tpi alternate set) welded to a tough alloy steel body

Bonded construction reduces possibility of shattering

For use with ferrous and non ferrous metals, plastics and wood to a depth of 32mm

14 to 30mm dia saws require a 6.5mm arbour

32 to 152mm dia saws require a 9.5mm arbour

Arbours, pilot drills and core removal tools available

RS Bi-metal hole saws



ENGLISH

Specifications:

Diameter	92mm
Material	M3 HSS Teeth; Alloy Steel Body
Cut Depth	32mm
Bimetal	Yes