

REVISIONS			
DATE	LTR	DESCRIPTION	APVD

ELECTRICAL




CURRENT RATING
5 Amp

DIELECTRIC WITHSTANDING VOLTAGE
AC 1000V Min. (for 1 minute)

INSULATION RESISTANCE
1000M Ω Min. (at 500V DC)

CONTACT RESISTANCE
25m Ω Max. mated

WORKING TEMPERATURE
-55°C to +105°C



UNLESS OTHERWISE SPECIFIED TOLERANCE : X ± 0.2 ANGLES : $\pm 2^\circ$ XX ± 0.1 XXX ± 0.05 DO NOT SCALE DRAWING		TITLE 25Way Mini Gender Changer	
DRAWN BY <i>Arhaa</i>	SCALE 1 : 1	AMT A	PART NO. 218-201
CHECKED BY <i>W. J. ...</i>	SCALE 1 : 1	THIRD ANGLE PROJECTION	PAGE 1 OF 1
APPROVED BY <i>A. J. ...</i>	DWG NO. DEWX2001061901X0	ITEM NO. MGCD25F/D25F-01E	DATE 08/19/2001

4	Label , Yellow Color
3	Hex Screw Nut #4-40
2	Hex Screw #4-40
1	D-SUB 25PIN Female, Gold Plated Over Nickel Contact , Blue PBT Insulator , Tin Plated Shell
No.	DESCRIPTION