




ELECTRICAL :

- CURRENT RATING
5 Amp Max.
- CONTACT RESISTANCE
25mΩ Max.
- INSULATION RESISTANCE
1000M Ω Min. (at 500V DC)
- DIELECTRIC WITHSTANDING VOLTAGE
AC 1000V (r.m.s.) Min. (for 1 minute)
- OPERATING TEMPERATURE
-55°C to +105°C



UNLESS OTHERWISE SPECIFIED TOLERANCE : K ±0.2 ANGLES : ±2° XJ ±0.1 XJK ±0.05 DO NOT SCALE DRAWING		TITLE 15 Way Mini Gender Changer			
DRAWN BY <i>Arhua</i>	SIZE	UNIT	PART NO.	218-217	
CHECKED BY <i>[Signature]</i>	SCALE	1 : 1	THIRD ANGLE PROJECTION	PAGE 1 OF 1	
APPROVED BY <i>[Signature]</i>	ENG. NO.	DEWX2001061901X0	ITEM NO.	MGCD15M/D15M-01E	DATE 06/19/2001

3	Label , Yellow Color
2	#4-40 Hex Screw
1	D-SUB 15 Male
No.	DESCRIPTION