



ENGLISH

Datasheet

Stock No: 231-964

RS Pro PTFE Tape for Sealing



Product Details

PTFE One Wrap Tape

Extra thick PTFE tape designed for sealing threaded joints in just one wrap.

Only requires 50% overlap on threads for BS21 thread up to 2 inch.

Reduced material usage.

For sealing against all common gases and liquids.

Length 5 m.

Suitable for potable water.

Satisfies BGC IM/16, BS 6974: 1989 and BS5292 Type C tests.

Conforms to BS7786 1995 Grade H.

PTFE Tapes



ENGLISH

Specifications:

Width	12mm
Thickness	0.2mm
Length	5m
Application	Sealing
Minimum Operating Temperature	-200°C
Maximum Operating Temperature	+260°C
Operating Temperature Range	-200 → +260 °C