

SOFT TINNED COPPER WIRE BRAID 2534P

CONSTRUCTION : 24x10x0.20MM
RESISTANCE : 2.3 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.
YIELD : 80.4KGS/1000M
TENSILE : N/A
WIRE : MANUFACTURED TO BSEN 13602: 2002
RoHS : COMPLIANT

