



SPECIFICATION SHEET 365559

SOFT TINNED COPPER WIRE BRAID 2536P

CONSTRUCTION : 24x12x0.20mm

CSA : 9.05mm²

RESISTANCE : 1.91 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.

YIELD : 96.5KGS/KM

TENSILE : N/A

WIRE : MANUFACTURED TO BS4109 C101.0

RoHS : COMPLIANT