



ENGLISH

Datasheet

RS 0.71 mm Transparent PTFE Cable Sleeve, 5m Length

RS Stock 404-516



Specification

| | | | | |
|------------------------|-------------------------------------|-------------------------|-------------------------|----------|
| Continuous temperature | -20 to 70 °C | -20 to 85 °C | -40 to 105 °C | |
| Insulation resistance | 10 ¹⁰ Ohm/cm | 10 ¹⁰ Ohm/cm | 10 ¹² Ohm/cm | |
| Dielectric strength | 20 kV/mm | 20 kV/mm | 25 kV/mm | 25kV/mm |
| Tensile strength | 15 MPa | 15 MPa | 18 MPa | |
| Elongation at break | 220% | 220% | 250 % | |
| Hardness | BSS20-30 | | BSS20-30 | BSS25-35 |
| Flammability | self extinguishing in 30 seconds | | | |
| Specification | N.A. | BS2848/3/85T | BS2848/3/105T | |
| RoHS compliant | yes | yes | yes | |