

Professionally approved products.

Datasheet

Uninsulated Crimp Spade Connector, 22 → 16 AWG, M3.5

RS Stock number [433-062](#)



Insulation Colour	Wire Range Mm ² /Awg	Stud Size	Dimension (mm)
Red	0.5-1.5mm ² /22-16AWG	#6/3.7	6.4/6.5/19.7/10.0/4.0/1.7/0.8

Specifications:

1. Maximum Electric Current: (最大電流)

22-16AWG / 0.5-1.5mm²: 19A

16-14AWG / 1.5-2.5mm²: 27A

12-10AWG / 4-6mm²: 48A

2. Terminal Body: Copper (端子材質: 紅銅)

3. Insulation: (護套材質:)

4. Plating: Tin (表面處理: 鍍錫)

NBT—Non-Insulated butted seam

NB—Non-insulated brazed seam