

Professionally approved products.

Datasheet

T-bar Tap Wrench

RS Stock Number [444-924](#)



Description:

Collet type with forward/lock/reverse operation ratchet.

Ideal for use in difficult to access areas.

Plated finish.

Thread sizes are: M5 to M12, 1BA to 0BA (ISO), 7/32 to 3/8 in (ISO), 1/4 to 3/8 in (DIN) BSW, M5 to M12 (ISO), M5 to M10 (DIN), #12 to 1/2 in (ISO), 1/4 to 3/8 in (DIN) UNF

Specifications:

Material:	Steel
Type:	Long Tap with Ratchet, Collect Ratchet
Handle:	120 mm
Height:	290 mm
A/F Range:	3.0 – 7.1 mm
Chuck Body Diameter:	25 / 24 mm
Length (T-bar to Chuck):	265 mm



Professionally approved products.

Tap Range:

Square	ISO 529	ISO 529	DIN 352	ISO 529	ISO 529	ISO 529	ISO 529	ISO 529	ANSI
Dimensions	Metric Coarse	Metric Coarse Relieved Shank	Metric Coarse	BSW	BSF	UNC	UNF	BA	NPT
	Full Diameter Shank with Recess								
Size mm	Size	Size	Size	Size	Size	Size	Size	Size	Size
3									
3.15	M4	M5		5/32					
3.3			M4						
3.5								3	
3.55	M4.5	M6							
3.8			M4.5						
4	M5			3/16	3/16			2	
4.2			M5						
4.5		M7							
4.9								0	
5	M6	M8	M6	1/4	1/4	1/4	1/4		
5.6	M7	M9							
5.9									1/16
6			M7						
6.3	M8	M10, M11		5/16, 7/16	5/16, 7/16	5/16, 7/16	5/16, 7/16		
6.8			M8						
7.1	M9	M12		1/2	1/2	1/2	1/2		