

SOFT TINNED COPPER WIRE TERMINATED BRAID

CONSTRUCTION : 24x10x0.20MM

LENGTH : 200MM

RESISTANCE : 2.31 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.

YIELD : 80.43KGS/1000M

TENSILE : N/A

WIRE : MANUFACTURED TO BS EN 13602:2002

RoHS : COMPLIANT

