

Professionally approved products.

Datasheet

Self Amalgamating Tape

RS Stock number [494-461](#)



Description:

A non-adhesive, polythene self-amalgamating tape with an easily removed interleave.

Strong

Elastic

Water resistant

Ozone resistant

Easily applied

Resistant to a wide range of chemicals including alkalis, hydraulic fluids and vegetable oils

High dielectric strength



Professionally approved products.

Specifications:

Thickness:	0.75 mm
Breaking Load:	12.0 N/cm
Elongation:	600 %
Electrical Strength:	34 kV/mm
Operating Temperature:	-35 °C to 130 °C
Application Temperature:	0 °C to 40 °C
Storage Temperature:	12 °C to 25 °C
Length:	10 m
Colour:	Black
Backing Material:	PE
Tensile Strength:	120 kg/cm ²
Width:	19 mm