

Professionally approved products.

Datasheet

Mica Capacitor

RS Stock number [495-975](#)



Specifications:

- Capacitance: 33000pF
- Construction: Radial
- Series: D
- Depth: 9.14mm
- Height: 22.61mm
- Length: 36.58mm
- Lead Pitch: 26.67mm
- Max. Operating Temperature: +150°C
- Min. Operating Temperature: -55°C
- Tolerance: ±1%
- Voltage: 500 Vdc