



ENGLISH

Datasheet

Stock No: 512-244

RS Pro PTFE Tape for Glass Joining, Heat Exchangers, Hydraulic & Pneumatic Systems, Pressure Flanges



Product Details

PTFE Sealing Strip

A closed cell polytetrafluoroethylene (PTFE) foam with a silicone placement adhesive on one side. The material is resistant to solvents, chemicals and corrosive gases. It will not contaminate contact surfaces but due to its compressibility will form a high pressure seal between glass, ceramic and metals. Typical applications are pressure flanges, heat exchangers, glass joints, hydraulic/pneumatic systems.

PTFE Tapes



ENGLISH

Specifications

Width	7mm
Thickness	2.5mm
Length	2m
Application	Glass Joining, Heat Exchangers, Hydraulic & Pneumatic Systems, Pressure Flanges
Minimum Operating Temperature	-196°C
Maximum Operating Temperature	+260°C
Operating Temperature Range	-196 → +260 °C