



Datasheet

Stock No: 512-635

RS Pro Hydraulic Spin-On Filter Can, 10µm, 95L/min 1-1/4 in



Product Details

RS Pro Spin-on Heads and Filters

An RS Brand range of Spin-On filters which can either be used as suction filters or as return line filters as they are ideally suited to low pressure applications.

Aluminium filter head

NBR (Buna-N®) sealings

Port connections: BSP, NPT, SAE Flange, SAE O-ring thread

Up to 14 bar / 200 PSI operating pressure

Up to 460 l/min / 120 US GPM nominal flow rate

Note

Use Glass Fibre Elements for longer lasting filtration with absolute 10 micron.

Medium & Low Pressure

Filters designed for use in medium or low pressure hydraulic systems. Installed downstream of the pump, they protect critical hydraulic components against dirt and other foreign matter generated within the pump.





Specifications

Filtration Size	10µm
Maximum Flow Rate	95L/min
Connection Thread	G 1-1/4
Seal Material	Nitrile Rubber
Maximum Operating Pressure	12 bar
Thread Size	1-1/4 in
Thread Standard	G
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-32°C