

Professionally approved products.

Datasheet

Insulated Crimp Blade Terminal 10mm Blade Length, 12 → 10 AWG, Yellow

RS Stock number [534-525](#)



Specifications:

1. **Maximum Electric Rating:** 75°C 600V

最高溫度: 75°C 耐壓 600V

2. **Maximum Electric Current:** (最大電流)

22-16AWG / 0.5-1.5mm²: 19A

16-14AWG / 1.5-2.5mm²: 27A

12-10AWG / 4-6mm²: 48A

3. **Terminal Body:** Copper (端子材質: 紅銅)


4. **Insulation:** Vinyl (護套材質: PVC)

5. **Plating:** Tin (表面處理: 鍍錫)

VM—Flared Vinyl without copper sleeve

PIPG—Pre-insulated funnel Vinyl insulator with easy entry copper sleeve

Professionally approved products. Datasheet



Insulation Colour	Wire Range Mm ² /Awg	Dimension (mm)
Yellow	4-6mm ² /12-10AWG	3.0/10.0/23.5/13.5/6.3/3.4/1.0