



ENGLISH

Datasheet

RS Pro Crimp Ring Terminal

RS Stock No: **534-193A**



Product Details

RS Pro crimp ring terminal is made from copper with flared vinyl or nylon (mini yellow) insulation. These insulated crimp ring wire connectors are colour coded for use with different wire sizes including mini yellow 0.2 - 0.5 mm² and are available with a variety of stud sizes.

Specifications:

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Inner Ring Diameter	6.4 mm
Insulation Material	PVC
Insulation	Insulated
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Outer Ring Diameter	11.6 mm
Overall Length	26.7 mm
Stud Size	1/4 in
Thickness	0.8 mm
Wire Size	22 to 16 AWG
Temperature Rating	+75°C
Voltage Rating	600 V
Amperage Rating	9 to 18 A
Type	Flared Vinyl without Copper Sleeve