



ENGLISH

Datasheet

Stock No: 687-326

RS Pro Swivel Plate Castor 361RNBR, 90kg



Product Details

Super Elastic Blue Rubber Tyre Castor, Series 61//88

Zinc plated body

Blue, non-marking tyre

Medium Duty Range with bright zinc finish

Pressed steel bracket with ball bearing swivel head

Thread guards available on Nylon wheeled castors

Threaded stem and triangular plate fitting options

Load Capacities of 27 - 680kg

Double ended footbrake option on 100mm sizes

Swivel radius on braked castors increases by 29mm.

Wheel sizes from 50mm to 150mm



ENGLISH

Specifications:

Wheel Diameter	75mm
Load Capacity	90kg
Overall Height	95mm
Wheel Width	32mm
Fixing Plate Dimensions	102 x 64mm
Rotation	Swivel
Application	Industrial
Tyre Material	Rubber
Includes Brake	Yes
Fixing Centres	80 x 60mm
Weight Class	Medium Duty
Features	Non-Marking
Number of Fixing Holes	4
Fixing Hole Size	8mm
Hub Bearing Type	Plain Bore
Hub Material	Nylon
Fixing Centres Length	83mm
Fixing Plate Length	102mm
Fixing Plate Width	64mm
Fixing Centres Width	35mm