



ENGLISH

Datasheet

Stock No: 814-023

RS Pro Female UNC 4-40 Screwlock For Use With D Connector



Product Details

Zinc Plated Screwlock Assemblies

- Assemblies consisting of three types: Male clip; Female (8mm thread length);
- Female (13mm thread length), extended thread for plastic flange 'D' connectors
- Thread size is 4-40 UNC
- Supplied disassembled

Specifications:

Type	Screwlock
Thread Size	UNC 4-40
Screw Length	8mm
Connector Type	D Connector
Screwlock Gender	Female
For Use With	D Connector
Finish	Zinc
CAD Drawing	3D CAD Model