



ENGLISH

## Datasheet

Stock No: 821-273

# RS Pro Stainless Steel Compression Spring



## Product Details

### Stainless Steel Compression Springs

Material to DIN 17224 No.1, 4310 or BS2056 EN58A

Ends are squared and unground

Appearance: brown/bronze

Made with a right hand helix

### Note

The load at minimum working length is the load required to compress the spring to that length. All dimensions and forces to conform to DIN 2095 (grade 2).



ENGLISH

## Specifications:

Outside Diameter	3.52mm
Wire Diameter	0.32mm
Free Length	29.3mm
Minimum Working Length	8.9mm
Load at Minimum Working Length	3.16N
Material	Stainless Steel
Spring Rate	0.16N/mm
Ends	Closed (Square)/Unground