



ELECTRICAL :

- CURRENT RATING
5 Amp Max.
- CONTACT RESISTANCE
25mΩ Max.
- INSULATION RESISTANCE
100M Ω Min. (at 500V DC)
- DIELECTRIC WITHSTANDING VOLTAGE
AC 1000V (r.m.s.) Min. (For 1 minute)
- OPERATING TEMPERATURE
-55°C to +105°C

UNLESS OTHERWISE SPECIFIED TOLERANCE : X ±0.1 ANGLES : ±2° XX ±0.1 XXX ±0.15 DO NOT SCALE DRAWING		TITLE 25 Way Port Protector			
DRAWN BY <i>Andy</i>	CHECKED BY	SIZE A	UNIT MM	PART NO. 828-252	
APPROVED BY <i>[Signature]</i>		SCALE 1 : 1	THIRD ANGLE PROJECTION ⊙ ←	PAGE 1 OF 1	
DWG NO. IEWX2001061901XJ		ITEM NO. MGCD25F/D25M-01E		DATE 12/18/2002	

No.	DESCRIPTION
3	#4-40 Hex Screw
2	D-SUB 25 Female
1	D-SUB 25 Male