



ENGLISH

Datasheet

Stock No: 821-318

RS Pro Stainless Steel Compression Spring



Product Details

Stainless Steel Compression Springs

Material to DIN 17224 No.1, 4310 or BS2056 EN58A

Ends are squared and unground

Appearance: brown/bronze

Made with a right hand helix

Note

The load at minimum working length is the load required to compress the spring to that length. All dimensions and forces to conform to DIN 2095 (grade 2).



ENGLISH

Specifications:

Outside Diameter	5.4mm
Wire Diameter	0.4mm
Free Length	53mm
Minimum Working Length	12.8mm
Load at Minimum Working Length	3.64N
Material	Stainless Steel
Spring Rate	0.09N/mm
Ends	Closed (Square)/Unground