


TOOLING NO.

CN50: 950648

HPPD868M: 950863

REVISIONS

DATE	LTR	DESCRIPTION	APVD



Specifications

Shielding	100% of Mylar Foil
Current Rating	500mA max
Working voltage	30V/DC max
Temperature Rating	80°C

PIN ASSIGNMENT :

P1	1	26	2	27	3	28	4	29	5	30	6	31	7	32	8	33	9	34	10	35	11	36	12	37	13	38	14	39	15	40	16	41	17	42	18	43
	PAIR 1		PAIR 2		PAIR 3		PAIR 4		PAIR 5		PAIR 6		PAIR 7		PAIR 8		PAIR 9		PAIR 10		PAIR 11		PAIR 12		PAIR 13		PAIR 14		PAIR 15		PAIR 16		PAIR 17		PAIR 18	
P2	6	40	7	41	8	42	9	43	10	44	11	45	12	46	13	47	14	48	15	49	16	50	17	51	18	52	19	53	20	54	21	55	22	56	23	57
	PAIR 19		PAIR 20		PAIR 21		PAIR 22		PAIR 23		PAIR 24		PAIR 25		shell																					
	19	44	25	45	21	46	22	47	23	48	24	49	25	50	shell																					
	PAIR 19		PAIR 20		PAIR 21		PAIR 22		PAIR 23		PAIR 24		PAIR 25		shell																					
	24	58	25	59	26	60	27	61	28	62	29	63	30	64	shell																					

TABLE

Part No	Length(X)
182-3977 CC50ME68M28500033AM-01E	1000±25
182-3999 CC50ME68M28500100AM-01E	3000±50

6	1	MI	W90HBE25PXXX01	UL2990 28AWS+25TW/PR+AL/Foil+Drain +Braid Jacket: Beige Color.
5		mm	2-1487213-9	Copper Foil 360° Soldered.
4		KG	8-1487208-5	Inner Molded PE.
3		KG	0-1487209-5	Overmolded PVC, Color: Beige
2	1	EA	6-1487179-1	CN50 Male, Contact: Gold Flash, Solder Type, Shell: Nickel Plated, Insulation: Black, PBT UL94V-0
1	1	EA	contact	HPDB65 Male, Contact: Gold 10U" Plated, Shell: Nickel Plated, Insulation: Black, Pitch: 1.27mm, W/Spring. Latch, Steel Nickel Plated, PBT UL94V-0
ITEM	QTY	U/M	PART NO.	DESCRIPTION

UNLESS OTHERWISE SPECIFIED,  
TOLERANCE :  
X .±0.2 ANGLES : 42°  
X.X ±0.1  
X.XX ±0.05 100° NOT SHAR PROTRU

DRAWN BY	Zhengjing	TITLE	HPDB68 Male To CN50 Male	
CHECKED BY	<i>[Signature]</i>	SIZE	A4	PART NO. 182-39XX
APPROVED BY	<i>[Signature]</i>	SCALE	1:1	THIRD ANGLE PROJECTION
DWG NO.	DEWJ2001050901X0	ITEM NO.	CC50ME68M28500033AM-01E	PAGE 1 OF 1
				DATE 08/17/2001