



## **Datasheet**

Stock No: 201-2768

# RS Pro Black Rubber Tyred Wheel, 160kg



### **Product Details**

#### Elastic Rubber Tyred Wheels

Solid Black Rubber tyre, hardness Shore 68A Excellent smooth and noiseless running High resistance to abrasion Temperature range -20°C to +70°C

#### Industrial - Elastic Tyre

Elastic rubber has a high load capacity, high wear resistance and gives a smooth, soft, cushioned ride. Temp  $-20^{\circ}$ c to  $+60^{\circ}$ c.



# ENGLISH

## Specifications:

Load Capacity	160kg
Tyre Type	Solid
Tyre Material	Rubber
Hub Material	Aluminium
Features	Abrasion Resistant, Quiet Operation
Hub Bearing Type	Ball Bearing
Wheel Diameter	100mm
Wheel Width	40mm
Bore Diameter	12mm
Bore Length	40mm
Colour	Black