

ENGLISH

Datasheet

RS Pro Uninsulated Crimp Spade Connector, 1.5mm² to 2.5mm², 16AWG to 14AWG, M5 Stud Size

RS Stock No: 208-2650



Product Details

RS Pro uninsulated crimp spade connector suit cables from 1.5 to 2.5 mm², 16 to 14 AWG with M5 stud size. It is suitable for ratchet action tool and basic plier action tool and is unshrouded.

Features and Benefits

- Suit cables from 0.5 to 1.5 mm² and 1 to 2.5 mm²
- Uninsulated
- Unshrouded



ENGLISH

Specifications:

Contact Material	Copper
Contact Plating	Tin
Insulation	Uninsulated
Shrouded	Unshrouded
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm²)	2.5 mm²
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm²)	1.5 mm²
Overall Length	21.25 mm
Stud Size	M5.3
Thickness	0.8 mm
Width	9.5 mm
Wire Size	16 to 14 AWG
Current Rating	27 A
Temperature Rating	+75°C
Type	Butted Seam Barrel
Voltage Rating	600 V