

Professionally approved products.

Datasheet

Conn;Rect;Pluggable/IO;Receptacle CXP

RS Stock number [214-9731](#)



Specifications:

Mating force : 210N min.

Unmating force : 42N min.

Durability : 250 cycles

Max. PCB insertion force : 25N per pin

Current rating : 0.5 amps max. per pin

Electrical

Connector signal integrity performance meets requirements of InfiniBand CXP specification

Enhanced footprint (EF) offers superior isolation at the board termination

Fully shielded and bezel gasket integrated for EMI containment

Applications:

Controller Cards and Servers

Network Switches

Routers

Storage Devices

Direct Attached Storage (DAS)

Storage Attached Networks (SAN)

Network Attached Storage (NAS)