

Datasheet

IEC Heavy Duty Thermocouple with Stainless steel probe 4.5mm x 150mm type J or K



- Type J or K thermocouple
- Stainless steel probe 4.5mm x 150mm
- 2 metres stainless steel over braided cable 7/0.2mm
- Temperature rating -60°C to +350°C
- Grounded measuring junction

Specifications:

Sensor type:	Type J or K thermocouple to IEC 584
Construction:	Stainless steel probe 4.5mm diameter x 150mm long, junction grounded to sheath at tip
Lead type:	2 metres glassfibre extension cable with stainless steel overbraid, 7/0.2mm conductors
Lead termination:	Bare wire tails
Temperature range:	-60°C to +350°C

Thermocouple type	Product code	Allied Code	RS order code
Type J	FAA-GSJ-4.5-150-2.0-C4-T	70641638	219-4725
Type K	FAA-GSK-4.5-150-2.0-C4-T	70651743	762-1128