



MA 001B (DB9F/25M ADAPTOR)

PIN OUT: 9Female 25Male

1	-----	8
2	-----	3
3	-----	2
4	-----	20
5	-----	7
6	-----	6
7	-----	4
8	-----	5
9	-----	22
G	-----	G

Label: orange color with white character

One side: SERIAL PORT ADAPTORS D9/D25

The other side: MINI ADAPTER

SPECIFICATION

INSULATOR: PBT Glass fibre reinforced III. 94 V0

CONTACT: Brass

CONTACT PLATING: Gold plated over nickel

SHELL: Tin plated shell

CURRENT RATING: 3 AMP

DIELECTRIC STRENGTH: 500V AC for one minute

INSULATOR RESISTANCE: 500MΩ min at 500V DC

TEMPERATURE: -25°C — +105°C

UNLESS OTHERWISE SPECIFIED				
TOLERANCE :				
X	±0.2	ANGLES :	±2°	
XX	±0.1			
XXX	±0.05	DO NOT SCALE DRAWING		
DRAW BY	<i>Andy</i>	TITLE Mini Serial Port Adaptor 9 Way Female To DB25 Male		
CHECKED BY	<i>Andy</i>	SIZE	UNIT	PART NO 243-0352
APPROVED BY	<i>Andy</i>	SCALE	1 : 1	THIRD ANGLE PROJECTION
DWG NO.	DEWX2001081901X0	ITEM NO.	MGCD091/D25M/09-02E	AGE 1 OF 1
			DATE	5/8/2002