



MA 001A (DB9M/25F ADAPTOR)  
 PIN OUT: 09Male 25Female

1	-----	8
2	-----	3
3	-----	2
4	-----	20
5	-----	7
6	-----	5
7	-----	4
8	-----	5
9	-----	22
G	-----	G

Label: orange color with white character  
 One side: SERIAL PORT ADAPTORS D9/D25  
 The other side: MINI ADAPTER  
 SPECIFICATION  
 INSULATOR: PBT Glass fibre reinforced UL 94 V0  
 CONTACT: Brass  
 CONTACT PLATING: Gold plated over nickel  
 SHELL: Tin plated shell  
 CURRENT RATING: 3 AMP  
 DIELECTRIC STRENGTH: 500V AC for one minute  
 INSULATOR RESISTANCE: 500MΩ min at 500V DC  
 TEMPERATURE: -25°C — +105°C

UNLESS OTHERWISE SPECIFIED TOLERANCE : X ±0.2 ANGLE : ±2° X.3 ±0.1 X.33 ±0.05 DO NOT SCALE DRAWING					
DRAWN BY: <i>Andy</i>		TITLE: Mini Serial Port Adaptor 9 Way Male To 25 Way Female			
CHECKED BY: <i>[Signature]</i>	SIZE: A	UNIT: MM	PART NO. 243-0368		
APPROVED BY: <i>[Signature]</i>	SCALE: 1:1	THIRD ANGLE PROJECTION		PAGE 1 OF 1	
DWG NO. DEWX2001061901X0	ITEM NO. MGCD08M/D25F-02E	DATE: 5/8/2002			