



ENGLISH

Datasheet

Stock No: 414-1509

RS Pro Single Tube Clamp



Product Details

Hose Clamps

Smooth internal profile allows firm grip over total contact area

Chamfered edges eliminate hose cover damage when in use

Can be used in conjunction with the Parker range of No-Skive hoses

Polypropylene body with zinc plated, passivated steel top plate and steel weld plate

Temperature range -30°C to +90°C

Note

Assembled clamp unit consists of weld plate, clamp body, top plate and M6 hexagon headed bolts.

Specifications

Number of Tubes Held	Single
For Tube Outside Diameter	38mm
Clamp Spacing	2m
Body Material	PP
Maximum Operating Temperature	+90°C
Maximum Tube Outer Diameter	38mm
Minimum Operating Temperature	-30°C