



ENGLISH

Datasheet

Stock No: 283-8302

# RS Pro Stainless Steel, Steel Hydraulic Check Valve, G 3/8



## Product Details

### Steel Non-return Valves

Manufactured from steel these non-return valves are seated metal to metal by means of spring loaded ball housed in an ABS plastic guide.

### Note

Not suitable for use with water.

Check Valves



## Specifications

Manufacturer Series	FT260
Connection Port Thread	G 3/8
Maximum Flow Rate	30L/min
Body Material	Stainless Steel, Steel
Maximum Operating Pressure	350 bar
Thread Standard	G
Thread Size	3/8 in
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C