

**ENGLISH** 

#### **Datasheet**

# RS Pro HSS M6 76 mm Counterbore Drill Bit, 11mm Cutter Diameter, 6 mm Screwed Shank

RS Stock No: 522-7446



#### **Product Details**

RS Pro counterbore drill bit has HSS construction with M6 thread size. This 76 mm long drill bit has a cutter diameter of 11 mm and screwed shank diameter of 6 mm. The right hand cutting counterbore is designed to produce recessed holes for cap headed screws.

#### **Features and Benefits**

- 12.5 mm cutter length
- 11 mm pilot length
- Pilot diameter of 6.4 mm
- Threaded shank
- 76 mm overall length
- Made from HSS



## **ENGLISH**

### **Specifications:**

| Cutter Diameter  | 11 mm   |
|------------------|---------|
| Cutter Length    | 12.5 mm |
| Material         | HSS     |
| Overall Length   | 76 mm   |
| Pilot Diameter   | 6.4 mm  |
| Pilot Length     | 8 mm    |
| Shank Diameter   | 6 mm    |
| Shank Type       | Screwed |
| Thread Size      | M6      |
| Number of Flutes | 2       |
|                  |         |