



Datasheet

Stock No: 324-4950

ENGLISH

RS Pro Stainless Steel, Steel Hydraulic Check Valve, BSP 3/8



Product Details

Stainless Steel Check Valves

Stainless steel BSP in-line check valve.

- Metal to metal seal by means of a machined cone
- BSP female thread forms

Specifications:

Manufacturer Series:	FT257
Connection Port Thread:	BSP 3/8
Maximum Flow Rate:	40L/min
Body Material:	Stainless Steel, Steel
Maximum Operating Pressure:	400 bar
Thread Standard:	BSP
Thread Size:	3/8 in
Minimum Operating Temperature:	-20°C
Maximum Operating Temperature:	+200°C