

Datasheet Stock No: 331-6364 RS Pro 6P6C Straight Cable Mount RJ11 Modular Plug Connector



Product Details

Modular Data Connectors

A comprehensive range of modular data plugs for networking, telecom and communications, offered in RJ10, RJ45, RJ11, and RJ22 versions, data connectors accept stranded cables from 26 - 24 AWG.

Features

- Gold plated phosphor bronze contacts
- 1.5 A Maximum current capacity
- 30 Vac 42 V dc rated voltage
- Polycarbonate body construction
- IDC contact termination

Specifications:

Gender:	Male
Number of Ways:	6P6C
Mounting Type:	Cable Mount
Orientation:	Straight
Contact Material:	Phosphor Bronze
Contact Plating:	Gold
Connector Type:	Modular Plug



Body material	Polycarbonate UL94V-0
Contact	Gold plated phosphor bronze
Current	1.5A max
Voltage	30V ac / 42V dc
Insulation resistance	500MΩ min
Contact resistance	20mΩ max

Compatibility		
Plug	Recommended cable	
331-6336	666-1109	
331-6342	666-1109	
331-6364	666-1103	
331-6370	666-1103	
331-6386	625-6782, 666-1115	