



ENGLISH

Datasheet

Stock No: 431-5592

**RS Pro Fahrenheit/Centigrade Dial Remote Mounting,  
Surface Mounting Dry Thermometer, Accuracy Class  
2**



## Specifications:

Thermometer Type	Dial
Fixing Method	Remote Mounting, Surface Mounting
Suitable Applications	Air Conditioning, Heating, Hot Water, Light Industrial, Ventilation
Temperature Scale	Both
Accuracy	Class 2
Filling Type	Dry
Case Material	Steel
Case Diameter	100mm
Maximum Temperature Sensed	+120°C
Minimum Temperature Sensed	0°C
Temperature Sensitive Range	0 → +120°C