



ENGLISH

Datasheet

RS Pro Crimp Tool BNC, TNC, RG58, RG59 Wire Size

RS Stock No: **473-0648**



Product Details

RS Pro crimp tool is a high quality low cost ratchet action tool for terminating both 50 Ω and 75 Ω connector ranges such as BNC, TNC, UHF, mini UHF and SMA, groups A and C. This tool is not suitable for BNC connectors utilising cable groups H, J, M, S or T.

Features and Benefits

- Supports RG58 and RG59 wire size
- BNC, TNC connector type
- Suitable for terminating both 50 Ω and 75 Ω connector



Specifications:

Crimp Connector Type	BNC, TNC
Maximum Wire Size	5.41 mm ²
Minimum Wire Size	1.72 mm ²
Wire Size	1.72 to 5.41 mm ²
Contact Resistance	<5 mΩ
Insulation Resistance	>1 x 10 ⁶ MΩ
Maximum Temperature	+70°C
Minimum Temperature	-20°C