

Datasheet

RS Pro 5mm Pitch Straight PCB Terminal Block with Screw Clamp Termination, Through Hole, 4 WayRS Stock No: **494-8928****Features and Benefits**

- Nickel plated bronze clamps, tin-plated brass terminals in glass filled PBT bodies
- Standard accepts wire 2.5 mm², low profile 1.5 mm²
- PBT construction

Specifications:

Body Orientation	Straight
Colour	Grey
Current Rating	16 A
Depth	12.5 mm
Gender	Male
Length	20 mm
Material	PBT



ENGLISH

Mounting Type	Through Hole
Number of Contacts	4
Number of Rows	1
Pitch	5 mm
Termination Method	Screw Clamp
Type	PCB Terminal Block
Voltage Rating	300 V
Width	9 mm
Insulation Resistance	1000 mΩ
Insulation Withstand Voltage	1000 V ac
American Wire Gauge	12 to 22 AWG
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-1