

ENGLISH

Datasheet

RS Pro 1/2 in BSP Stainless Steel Y Strainer

RS Stock No: 499-2723



Product Details

RS Pro stainless steel Y strainer has 1/2 in BSP connection that is suitable for use when the small amount of solids need to be removed. It can be installed in both horizontal and vertical positions. The strainer has standard BSP threads for easy connection. It is available in a variety of sizes.

Features and Benefits

- 1/4 3 Inch (DN8 DN80)
- Thread type: ASME B1.20.1 (NPT) DIN2999 and BS21 ISO 7/1 and EN10226
- W.P: 800WOG (PN50)
- W.T: -20 200°C
- · Investment casting



ENGLISH

Specifications:

Body Material	Stainless Steel
Connection	1/2 in BSP
Strainer or Filter	Strainer
Suitable Media	Liquid
Thread Standard or Connection Type	BSP
Connection Size	1/2 in
Maximum Working Pressure	40 bar