

ENGLISH

Datasheet

RS Pro Tap Wire Splice Connector, Red, Insulated 22 \rightarrow 18 AWG

RS Stock No: 510-4898



Product Details

RS Pro tap wire splice connector in red colour, is insulated and has wire size 22 to 18 AWG. This quick splice IDC wire splice connector made from brass with colour is, coded nylon insulation. This quick splice provides a simple and time saving wire connection method. The splice is simply placed over the existing wire, the additional wire inserted and the block crimped can then be crimped with pliers. This IDC quick splice is available for inline and T-tap wire connections and accepts various wire and tab sizes.

Features and Benefits

- Quick splice IDC wire splice connectors made from brass with a colour coded nylon insulation
- · Quick splice provide an simple and time saving wire connection method
- Splice is simply placed over the existing wire, the additional wire inserted and the block crimped can then be crimped with pliers



ENGLISH

Specifications:

Colour	Red
Contact Material	Brass
Insulation	Insulated
Insulation Material	Nylon
Shrouded	Shrouded
Splice Type	Тар
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm²)	0.75 mm ²
Minimum Wire Size (AWG)	20 AWG
Minimum Wire Size (mm²)	0.5 mm²
Overall Length	34 mm
Wire Size	20 to 18 AWG
Current Rating	12 to 17 A
Temperature Rating	+105°C
Voltage Rating	600 V
Width	35 mm