

**ENGLISH** 

#### **Datasheet**

# RS Pro Steel M8 87.3 mm Counterbore Drill Bit, 15mm Cutter Diameter, 10 mm Screwed Shank

RS Stock No: 522-7452



#### **Product Details**

RS Pro counterbore drill bit has steel construction with M8 thread size. This 87.3 mm long drill bit has a cutter diameter of 15 mm and screwed shank diameter of 10 mm. The right hand cutting counterbore is designed to produce recessed holes for cap headed screws.

#### **Features and Benefits**

- 19 mm cutter length
- 9.5 mm pilot length
- Pilot diameter of 8.4 mm
- Threaded shank
- 87.3 mm overall length
- Made from steel



## **ENGLISH**

### **Specifications:**

Cutter Diameter	15 mm
Cutter Length	19 mm
Material	Steel
Overall Length	87.3 mm
Pilot Diameter	8.4 mm
Pilot Length	9.5 mm
Shank Diameter	10 mm
Shank Type	Screwed
Thread Size	M8
Number of Flutes	2